



More information on the website
radwag.com/en/info,w1,ILW

XA 210.5Y Analytical Balance



XA 210.5Y Analytical Balance

The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit measurement



Statistics



Checkweighing



IR sensors



Under-pan weighing



GLP Procedures



Animal weighing



Pipettes Calibration



Air density correction



Density determination



Differential weighing



Ambient conditions monitoring



Statistical Quality Control



Packaged Goods Control



ALIBI Memory



Wi-Fi

Datasheet

	XA 210.5Y Analytical Balance
Metrological parameters	
Maximum capacity [Max]	210 g
Minimum load	1 mg
Readability [d]	0,01 mg
Verification unit [e]	1 mg
Tare range	-210 g
Standard repeatability [5% Max]	0,005 mg
Standard repeatability [Max]	0,025 mg
Standard minimum weight (USP)	10 mg
Standard minimum weight (U=1%, k=2)	1 mg
Permissible repeatability [5% Max]	0,012 mg
Permissible repeatability [Max]	0,035 mg
Linearity	±0,1 mg
Eccentric load deviation	0,1 mg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times \text{Rt}$
Stabilization time	4 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	semi-automatic - LevelSENSING
Display	10" touchscreen
Weighing chamber doors	manual
Delivery components	Analytical Balance, weighing pan, weighing pan shield, centring ring, bottom cover, brush, fabric dust cover, power supply.
Weighing chamber dimensions	168×160×228 mm
Weighing pan dimensions	ø90 open-work pan + ø85 (option) mm
Packaging dimensions	750×492×595 mm
Net weight	9,8 kg
Gross weight	14,3 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	USB-A ×2, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity change rate	±1%/h (±4%/8h)

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration Tables
Power Adapters
RS 232, RS 485 cables
Holders for laboratory flasks
Density determination KIT
Additional modules
Holders for test tubes and filters
Professional Weighing Tables
Protective cover for balances
Barcode scanners
Automatic feeders

USB Hubs
Label Printers
RS 232, RS 485 cables
THBR 2.0 System - Ambient Conditions Monitoring
Protective cover for balances
Under-pan weighing
Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Weighing dishes
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Under-pan weighing

Software

E2R System
Label Editor R02
R-LAB
RADWAG Development Studio

RAD-KEY
RADWAG Remote Desktop
Scales Editor 2.1

Device dimensions

XA 210.5Y Analytical Balance

